

igubal[®] 2.0 metallic rod ends

high strength with proven wear resistance and suitable for outdoor environments



Housing

- High load capacity
- Zinc die cast or stainless steel
- Right hand & left hand thread
- Male & female versions

Spherical ball

- Stainless steel
- Metric & inch dimensions

Bearing liner

- Maintenance-free
- High wear resistance
- Vibration dampening
- iglide[®] J & iglide[®] A181 for FDA
- iglide[®] X for high-temperature



Scan for more info

KCRI sizes in inch	KCRM sizes in mm	KARM sizes in mm
0.4375	6.0	6.0
0.5000	8.0	8.0
0.6250	10.0	10.0
0.7500	12.0	12.0
1.0000	16.0	16.0
1.2500	20.0	20.0



FDA

igus[®]

improve what moves

